



	DESCRIPTION	MEASUREMENT
A	RAIL WIDTH	
B	RAIL SETBACK	(A-6 15/16")
C	RAIL HEIGHT	32"
D	ANCHOR DEPTH	4" OR 6" SUGGESTED
E	NUMBER OF STEPS	
F	OVERALL DROP	
G	STEP SPACING	12" TYPICAL
H	ANCHOR SPACING	20" RECOMMENDED

**NOTE:**

Field measurements are required for the product you wish to order. Please provide accurate measurements to eliminate delays or errors in the design and manufacturing.

It is the responsibility of the customer to ensure the ladder meets all local and state codes.

X	MATERIAL
	1.90"x.065" 304L STAINLESS STEEL
	1.90"x.109" 304L STAINLESS STEEL
	1.90"x.145" 304L STAINLESS STEEL
	1.90"x.065" 316L STAINLESS STEEL
	1.90"x.109" 316L STAINLESS STEEL
	1.90"x.145" 316L STAINLESS STEEL
	1.50"x.083" 316L STAINLESS STEEL
	1.50"x.120" 316L STAINLESS STEEL

*NOTE:*

*△ DIMENSIONS VARY WITH SPECIFIC APPLICATIONS. SPECIFICATIONS ARE NOMINAL, AND ARE SUBJECT TO CHANGE. PLEASE CONTACT SPECTRUM AQUATICS FOR CUSTOM APPLICATIONS*

**SPECTRUM**  
Aquatics

A PLAYCORE Company

7100 Spectrum Lane  
Missoula, Montana 59808  
800.791.8056

www.spectrumaquatics.com

*ENGINEERING DATA*

PRODUCT:	SPECTRUM LADDER -		
MODEL #:	MG LADDER	CATALOG #:	REVISION: A
MATERIAL:	300 SERIES S.S. TUBE		
FINISH #:	PASSIVATE IAW ASTM A967		